

# ELECTRIC FILING PEDICURE BITS

USE ONLY THE FOLLOWING APPROVED BITS  
AT THE CORRECT ROTATION SPEED



## ELECTRIC PEDICURE

Cuticle clean Bit - MIN 3.000 - MAX 6.000 RPM - ref. 29259



6.000 RPM

Diamond Nail Prepper Cone - ref. 28564



6.000 RPM

MIN 6.000 - MAX 30.000 RPM

Tungsten Trimmer Bit - MIN 6.000 - MAX 15.000 RPM - ref. 29487



10.000 RPM



15.000 RPM

Diamond Grinder Bit - MIN 6.000 - MAX 30.000 RPM - ref. 29486



10.000 RPM



15.000 RPM

Diamond Ball Bit - MIN 6.000 - MAX 30.000 RPM - ref. 29485




10.000 RPM



15.000 RPM

Finisher Bit - MIN 6.000 - MAX 30.000 RPM - ref. 29484



6.000 RPM

## CALLUS REMOVAL

10.000 RPM

Ceramic Pedicure Callus bit - ref. 29721



10.000 RPM

Diamond Pedicure Callus bit - ref. 29722



15.000 RPM

Silicon Pedicure Polisher bit - ref. 29723



## CLEANING BITS

Cleaning brush for bits - ref. 29724

